



RIGOL



Newark

AN AVNET COMPANY



New Education Test Bench

Comparable performance, lower price. **RIGOL**

Brand	Bandwidth	Channels	Sample Rate	Memory	Price after Education Discount
RIGOL DH0802	70 MHz	2	1.25 GSa/s	25 Mpts	\$ 313
Brand-A	50 MHz	2	1 GSa/s	20 kpts	\$ 493
Brand-B	50 MHz	2	2 GSa/s	2 Mpts	\$ 1,232
Brand-C	50 MHz	2	1 GSa/s	200 kpts	\$ 638

Equipping a classroom or teaching lab? Check out RIGOL's new education test bench!

POWERFUL. COMPACT. AFFORDABLE.

RIGOL's series of ultra-portable instruments offer university engineering departments the ideal combination of functionality, performance, size and value. The combination of **DH0800 High-Resolution Oscilloscope**, **DG800 Pro Generator** and **DM858 Multimeter** makes for an ideal test bench for engineering students, with each instrument delivering impressive performance and touch-screen functionality in a compact and light form factor.



DH0800 High-Resolution Oscilloscopes

- 70 MHz to 100 MHz
- 2 or 4 Analog Channels

DG800 Pro Arbitrary Waveform Generators

- 25 MHz to 50 MHz
- 16 Bit Vertical Resolution

DM858 Digital Multimeters

- 5.5 Digit DMM
- 7" Touch Display

Outfitting research or design labs? RIGOL's educational discount applies to our entire portfolio – oscilloscopes, arbitrary waveform generators, spectrum analyzers, RF signal generators, multimeters, power supplies and electronic loads.

RIGOL
www.rigolna.com



Newark
AN AVNET COMPANY

www.newark.com