



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART
CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-FD05	Effective: 12/21/88	DCP No. 480
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE
170	A	RELEASED	HYO	2/11/00	JJC	2/11/00
						4/28/00



SPECIFICATIONS:

1. INSULATOR BODY: POLYACETAL
2. PLUG BODY: BRASS, NICKEL PLATED
3. SPRING CONTACT: BECU, NICKEL PLATED
4. VOLTAGE: 500V
5. CURRENT: 36A MAX.
6. TEMPERATURE: -20 °C TO +80 °C
7. MAXIMUM WIRE SIZES:
CONDUCTOR: Ø.090 (12AWG)
STRIP LENGTH: .25 (6.4)
8. COLOR: BLACK



ASSEMBLED

DISCLAIMER

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

Tolerances Unless Otherwise Specified

Fractions ± 1/32

Decimals .XX ± .01

.XXX ± .005

DRAWN BY: HISHAM ODISH

CHECKED BY: JOHN COLE

APPROVED BY: DANIEL CAREY

DATE: 2/11/00

DATE: 2/11/00

DATE: 4/28/00

DRAWING TITLE: DO-IT-YOURSELF 4mm PLUG, SOLDER ATTACHMENT

SIZE: A

DWG. NO.: 2305

SCALE: NTS

ELECTRONIC FILE: 92N4667.DWG

REV: A

SPC TECHNOLOGY

U.O.M.: INCHES [mm]

SHEET: 1 OF 1

SPC-FD05.DWG